

CS8 floorline bed

PERFECTLY STYLED



The Invacare CS8 bed is an electrically actuated care bed with a range of functions and positional movements that assist caregivers and provide for patient comfort. Ease of use, functionality, serviceability and cleaning practicality are key features of the bed.



CS8

CS8 floorline bed

The bed has a fabricated steel structure with a powder coated finish. The plastic components are made from urethane, PP, POM, nylon and ABS plastic.

Clinical Applications and Area of Use:

The bed is appropriate for adult patient care under supervised medical monitoring and provides support with various positioning options.



Features

- Total safe working load (SWL) of the bed 250Kg.
- 75mm twin Tente castors (four braking castors and four free-wheeling).
- Electrically adjusted height range. The bed works within a height range of 150mm low height to a maximum high height of 680mm.
- Trendelenberg head and foot down tilt 14°.
- Four sectioned electronically operated mattress platform with independent adjustment of backrest angle (maximum 65°) and knee section angle (maximum 35°).
- Four soft contoured mattress retainer handles.
- Integral foot end mattress base extension. Extends the bed by 195mm.
- (Optional) bolt on 3/4 length folding side rails.
- Removable timber head and foot panels.
- One button chair positioning.
- Under bed lighting.

Tech Specs

Basic Dimensions:

Overall Length	211.0cm
Overall Length (base extension extended)	230.5cm
Overall Width	92.0cm
Overall Width (rails fitted)	100.0cm
Mattress Surface Length (between panels)	199.5cm
Bed Platform Height Range	15.0cm to 68cm
Back Rest Angle Adjustment	0° to 65°
Knee Bend Angle Adjustment	0° to 35°
Trendelenberg Tilt Adjustment (head and foot down)	0° to 14°

Electric Parameter:

Power Input	100-240V AC 50/60Hz, Max current 2.5A
Rate Load	interruption 10%, Max 2 minutes / 18 minutes
Leakage Protection	Class 1 Type B
Waterproof Grade	IP54

Mattress Size:

Recommended Mattress Size	Width = 86.0cm
	Length = 198.0cm
Maximum Mattress Depth (when side rails in use)	17.0cm
Minimum Mattress Depth (when side rails in use)	10.0cm

Bed Weight & Safe Working Load:

Without Side Rails	119 Kg (approx)
With Side Rails	138 Kg (approx)
S.W.L Safety Factor = 2 x S.W.L	250Kg

Standard:

CS8 beds are designed and manufactured in compliance with International Standard IEC 60601-2-52 where applicable.

Size Options:

- Single
- King Single

FOR FURTHER INFORMATION:

New Zealand: Freephone 0800 468 222, email sales@invacare.co.nz or visit www.invacare.co.nz

Australia: Freephone 0800 460 460, email sales@invacare.com.au or visit www.invacare.com.au

Asia: Phone +61 2 8839 5330, email exportsales@invacare.com.au or visit www.invacare.com

Thailand: Phone +66 0 2108 8555 or visit www.invacare.com



Yes, you can.®